





Silent Drawer System

Modul Box Assembly Instruction

15.5


Front Fixing Brackets Positions

Back Panel Mounting Positions

Special Features:


- Length: 270,300,350,400,450,500,550mm.
- The drawer side-board is 88mm high.
- Drawer width can be designed freely with automatic error adjustment.
 Hidden full pullout silencing sliding skid can bear 35kg and enjoys excellent stability and quite and smooth sliding performance.
- Quick installation and dismantle.
- Newly-designed built-in damper is free from reinstallation and ensures soft and smooth drawer movements.

550mm	500mm	450mm	400mm	350mm	300mm	270mm	Basic length
524mm	474mm	424mm	374mm	324mm	274mm	244mm	Internally usable drawer depth
555mm	505mm	455mm	405mm	355mm	305mm	275mm	Minimum installation depth of drawer
110mm	Minimum installation height						




Mounting the drawer


(W)



Technology pivot:
Bottom and Back Panel Measurement
16MM Density Panel



32 min47.5



B Side overlay(user-defined)


Front panel removing


1 Loosen the fastening screws 2 Rotation to dismantle the pan Rotation to dismantle the panel


37 5±0 5


В


min47.5


































Installing the drawer





2

LW:Inside Cabinet Width
Bottom panel width=Inside Cabinet Width-75±0.5
Bottom panel length=Runner length-10MM Back panel height=68MM

Back panel width=Inside Cabinet Width-87±0.5

Basic length: 270/300/350/400/450/500/550

